

## **Product Technical Data Sheet**

# Ambic FoamDipper<sup>™</sup> ADC/130



#### **Properties**

Bottle: Low Density Polyethylene (LDPE)

Handle and Applicator: 402-CB12 Polypropylene

Foaming Insert: Polypropylene

Tube: Polyvinyl chloride (PVC)

Capacity: 250 ml bottle

Dimensions: 6.5 x 9 x 22 cm

Net Weight: 0.10 Kg

### **Features**

- Uses a special foaming insert which sits in the DipCup reservoir.
- Can be dismantled for cleaning.
- Easy squeeze action for rapid and consistent foam generation.
- · Available in a range of colours.
- Convenient belt hook.

#### Instructions

- Squeeze bottle to generate foam in the DipCup insert.
- Bring the cup up under the udder and over the teat.
- Push the cup all the way to the base of the udder.
- When the teat is inserted into the cup, it will displace the foam and cover the entire teat from the tip to the base.

Manufactured in the UK

EU Tariff Code: 39233010

REACH compliance is not applicable.